

1200 × 900

acniti LLC
1-2-9 Nyoidani
Minoh Osaka
562-0011
Japan



Ozone water concentration sensor

Sensor for measuring ozone concentrations levels from 0-20 mg/L in water. The working principle of the ozone concentration sensor is Lambert's cosine law, which is obtained via UV light.

Ozone water concentration sensor

Measure accurately ozone levels in water

- ✓ Ozone water concentration sensor 0-50 mg/L
- ✓ For high precision measurement of ozone concentrations
- ✓ Calibration performed automatically and can be set to frequent or infrequent calibrations
- ✓ Excellent ozone sensor for universities and research and development departments

Measure ozone in water

Measure ozone concentrations levels from 0-50 mg/L precisely in water. The unit measures ozone concentration with UV light, the sensor has a built-in self-priming suction pump to take in sample water and reference water. This unit is excellent for universities and research departments of companies. The sensor has a possibility to connect a recorder to collect data overtime. Furthermore, it has an ERR output and a "Hi Lo" output.

UV Technology

Ozone has a maximum absorption band near the wavelength of ultraviolet at 253.7 nanometers. A low-pressure mercury lamp light source has an emission line spectrum at 254 nm. By irradiating ozone with this wavelength, the amount of light without ozone gas (I₀) and the amount of light with ozone gas (I_x) are Lambertian. Lambert law : when an area element is radiating as a result of being illuminated by an external source, the irradiance (energy or photons/time/area) landing on that area element will be proportional to the cosine of the angle between the illuminating source and the normal.

The ozone concentration is obtained from Beer-Lambert law, and compared with a standard device calibrated by the iodine titration method to make a correction and use it as the display value at the end of calibration Beer-Lambert law relates the attenuation of light to the properties of the material through which the light is travelling.

Since the measured ozone concentration is inversely proportional to the gas or water temperature, most units are equipped with a temperature sensor. The temperature reading is used to autocompensate the ozone concentration output.

Polarograph polymeric membrane technology

The theory of this polarograph with polymeric membrane type dissolved ozone monitoring is generally used in the Electro chemistry analysis and has many use cases. Ozone in water consists of ozone ions, and will enter through the polymeric membrane into the working electrode, reacting the ions on its surface. On the counter electrode happens an equivalent reaction of oxidation on the surface, to which the electric current is proportional to the ozone concentration generated.

EL550 UV technology

The EL-550 is an ozone monitor that is intended to be incorporated into equipment, and has been made compact and reasonably-priced by minimizing functions other than analog output. It can be installed on the wall or on the floor to reduce restrictions on installation location.

EL610 UV technology

The EL-610 is a more advanced model ozone monitor than the EL-550. The sensor has more functionality and the sensor and the controller are separated which increases the freedom in installation.

CX-100 II

The CX-100 II is the most economical solution to measure dissolved ozone and other dissolved components such as trichloroethylene, tetrachloroethylene, 1.1.1 Trichloroethane, Carbon Tetrachloride, Ammonia (Ammonium ions), Hydrogen Sulfide. The sensor is not based on the UV method described above. The unit is easy to carry as it is battery powered. It can measure accurately water temperatures from 5°C to 35°C or 41°F to 91°F. Acniti recommends the CX-100 II for calibrating the ELP-200.

If you would like to read more about the CX-100 II read the blog post.

el-550 series

Beschreibung		Metrisch	Kaiserlich
1	Model name	EL-550 Series	EL-550 Series
2	Model number	EL-550	EL-550
Flüssigkeit		Metrisch	Kaiserlich
3	Minimum flow / minute	0.1 Liter	0.0 Gallone
4	Maximum flow / minute	3.0 Liter	0.8 Gallone
5	Minimum flow / hour	3.0 Liter	0.8 Gallone
6	Maximum flow / hour	180 Liter	48 Gallone
7	water temperature minimum	5 °C	41 °F
8	water temperature maximum	40 °C	104 °F
Umgebung		Metrisch	Kaiserlich
9	Ambient temperature minimum	5 °C	41 °F
10	Ambient temperature maximum	40 °C	104 °F
11	Relative humidity minimum	0 %	0 %
12	Relative humidity maximum	90 %	90 %
Elektrisch		Metrisch	Kaiserlich
13	Unit phase Ø voltage	100-220V ±10% AC50/60Hz	100-220V ±10% AC50/60Hz
14	Unit power consumption	50VA	50VA
15	Wetted parts	Synthetic quartz, PTFE, PFA	Synthetic quartz, PTFE, PFA
16	Pump pressure setting	0.3 MPa (G) or less	0.3 MPa (G) or less
Pumpe			

	Abmessungen & Gewicht	Metrisch	Kaiserlich
17	Abm. (B) x (T) x (H)	220 x 105 x 150 mm	8.7 x 4.1 x 5.9 Zoll
18	weight	2.2 Kg	4.9 lbs.

el-610 series

Beschreibung		Metrisch	Kaiserlich
1	Model name	EL-610 Series	EL-610 Series
2	Model number	EL-610	EL-610
Flüssigkeit		Metrisch	Kaiserlich
3	Minimum flow / minute	0.1 Liter	0.0 Gallone
4	Maximum flow / minute	3.0 Liter	0.8 Gallone
5	Minimum flow / hour	6.0 Liter	1.6 Gallone
6	Maximum flow / hour	180 Liter	48 Gallone
7	water temperature minimum	5 °C	41 °F
8	water temperature maximum	40 °C	104 °F
Umgebung		Metrisch	Kaiserlich
9	Ambient temperature minimum	5 °C	41 °F
10	Ambient temperature maximum	40 °C	104 °F
11	Relative humidity minimum	0 %	0 %
12	Relative humidity maximum	90 %	90 %
Elektrisch		Metrisch	Kaiserlich
13	Unit phase Ø voltage	100-220V AC, 50/60Hz	100-220V AC, 50/60Hz
14	Wetted parts	Synthetic quartz, PTFE, PFA	Synthetic quartz, PTFE, PFA
Abmessungen & Gewicht		Metrisch	Kaiserlich
15	Abm. (B) x (T) x (H)	220 x 105 x 150 mm	8.7 x 4.1 x 5.9 Zoll
16	weight	2.2 Kg	4.9 lbs.

Bemerkungen

17 Other remarks

- ✓ Sensor and processing in one compact unit
- ✓ High accuracy and stability
- ✓ Resistant to aggressive water conditions
- ✓ Clear display and intuitive calibration
- ✓ Simple connection to your operating systems

cx-100ii dissolved matter detector

Beschreibung		Metrisch	Kaiserlich
1	Model name	CX-100II Dissolved Matter Detector	CX-100II Dissolved Matter Detector
2	Model number	CX-100II	CX-100II
Flüssigkeit		Metrisch	Kaiserlich
3	water temperature minimum	4 °C	39 °F
4	water temperature maximum	30 °C	86 °F
Abmessungen & Gewicht		Metrisch	Kaiserlich
5	Abm. (B) x (T) x (H)	225 x 105 x 240 mm	8.9 x 4.1 x 9.4 Zoll
6	weight	2 Kg	4.4 lbs.

Bemerkungen

- | | |
|-----------------|--|
| | <ul style="list-style-type: none">✓ It is very small and lightweight and suitable for on-site measurement.✓ Since it is aerated in a closed container, it can measure even low concentrations with high sensitivity.✓ Calibration (standard solution) is not required during measurement✓ The sample collection volume is as small as 10 or 50 mL. |
| 7 Other remarks | <ul style="list-style-type: none">✓ There is no need for temperature compensation, and measurement variations among operators have been reduced.✓ Almost unaffected by coexisting substances in the sample.✓ The cleaning filter is not affected by ambient gas.✓ Dissolved ozone, trichlorethylene, tetrachlorethylene, dissolved sulfide, and ammonia can be measured simply by changing the detector tube. |